

DAC 選択ガイド



QSF2PXA1MBL



PHQ4SFP2A1MBL



PSF1PZA1MBU



PSF1PZA1MRD



PSF1PZA1MWH

トランシーバ詳細	長さ (m)	ケーブル色：黒	ケーブル色：青	ケーブル色：赤	ケーブル色：白	AWG
SFP+ 10G DAC	1	PSF1PZA1MBL	PSF1PZA1MBU	PSF1PZA1MRD	PSF1PZA1MWH	30
	1.5	PSF1PZA1.5MBL	PSF1PZA1.5MBU	PSF1PZA1.5MRD	PSF1PZA1.5MWH	
	2	PSF1PZA2MBL	PSF1PZA2MBU	PSF1PZA2MRD	PSF1PZA2MWH	
	2.5	PSF1PZA2.5MBL	PSF1PZA2.5MBU	PSF1PZA2.5MRD	PSF1PZA2.5MWH	
	3	PSF1PZA3MBL	PSF1PZA3MBU	PSF1PZA3MRD	PSF1PZA3MWH	
	3.5	PSF1PZC3.5MBL	PSF1PZC3.5MBU	PSF1PZC3.5MRD	PSF1PZC3.5MWH	26
	4	PSF1PZC4MBL	PSF1PZC4MBU	PSF1PZC4MRD	PSF1PZC4MWH	
SFP28 25G DAC	1	PSF2PZA1MBL	PSF2PZA1MBU	PSF2PZA1MRD	PSF2PZA1MWH	30
	1.5	PSF2PZA1.5MBL	PSF2PZA1.5MBU	PSF2PZA1.5MRD	PSF2PZA1.5MWH	
	2	PSF2PZA2MBL	PSF2PZA2MBU	PSF2PZA2MRD	PSF2PZA2MWH	
	2.5	PSF2PZA2.5MBL	PSF2PZA2.5MBU	PSF2PZA2.5MRD	PSF2PZA2.5MWH	
	3	PSF2PZA3MBL	PSF2PZA3MBU	PSF2PZA3MRD	PSF2PZA3MWH	
	3.5	PSF2PZC3.5MBL	PSF2PZC3.5MBU	PSF2PZC3.5MRD	PSF2PZC3.5MWH	26
	4	PSF2PZC4MBL	PSF2PZC4MBU	PSF2PZC4MRD	PSF2PZC4MWH	
QSFP28 100G DAC	1	QSF2PXA1MBL	—	—	—	30
	2	QSF2PXA2MBL	—	—	—	
	3	QSF2PXA3MBL	—	—	—	
	4	QSF2PXC4MBL	—	—	—	26
	5	QSF2PXC5MBL	—	—	—	
QSFP28 100G DAC to 4x25G SFP28 DAC Breakout	1	PHQ4SFP2A1MBL	—	—	—	30
	2	PHQ4SFP2A2MBL	—	—	—	
	3	PHQ4SFP2A3MBL	—	—	—	
	4	PHQ4SFP2C4MBL	—	—	—	26
	5	PHQ4SFP2C5MBL	—	—	—	