





2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN BRACKETS ARE METRIC.
3. MATERIAL: GALVANNEALED STEEL  
COLOR: BLACK
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. PART WEIGHT 3.0 lbs (1.4 kg)



REV						DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE				
00	7-18-16	SAT	BONS	TMK	RELEASED TO PRODUCTION					15F318AF-DC		2RU HD FLEX FRONT CABLE MANAGER				
											CUSTOMER DRAWING					
											ITEM REVISION NAME		15F318AF/01		<b>PANDUIT</b>	
											DATASET FILE NAME		15F318AF_DC/01A			
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) DIMENSIONS ARE FOR REFERENCE ONLY				PART NO. FLEX-FCM2UA	
											THIRD ANGLE PROJECTION		DRAWING NUMBER:		15F318AF-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE			SHT 1 OF 1	SIZE		
							SAT	7-14-16	BONS	1:8		A				

2

1