



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	FIBER TYPE	PERFORMANCE LEVEL	ADAPTER COLOR (SPLIT SLEEVE)
FQ6N-06-03AS	OM1	STANDARD LOSS	ELECTRIC IVORY (PHOS BRONZE)
FQ5N-06-03AS	OM2	STANDARD LOSS	BLACK (PHOS BRONZE)
FQXN-06-03AS	OM3	STANDARD LOSS	AQUA (ZIRCONIA)
FQXO-06-03AS	OM3	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQZN-06-03AS	OM4	STANDARD LOSS	AQUA (ZIRCONIA)
FQZO-06-03AS	OM4	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQ9N-06-03AS	OS1/OS2	STANDARD LOSS	BLUE (ZIRCONIA)

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
  - MODULE MATERIAL: PLASTIC
  - ADAPTER: COMPOSITE PLASTIC
- CASSETTE MODULE WEIGHT: 2.4oz [69.0g]
- DIMENSIONS IN BRACKETS ARE METRIC
- METHOD A CASSETTES COMPLY WITH ANSI/TIA-568-C.0. SEE ANSI/TIA-568-C.0. FOR POLARITY DETAILS AND EXAMPLE OF A BASIC LINK.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

PART NUMBER		FQ** - 06 - 3A3	
TITLE			
QUICKNET SFQ SERIES CASSETTE, 6 FIBER DUPLEX SC TO MPO CASSETTE METHOD A			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02947ZA/02	
DATASET FILE NAME		M02947ZA_DC/00C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ±		.xxx ± .010 [.3]	
.xx ± .03 [.8]		ANGLES ±	
DRAWN BY		SCALE	
EFK		NONE	
DATE		SHT 1 OF 1	
08-05-09		A	
CHK		DRAWING NUMBER:	
JAWI		02947-42	
SCALE		THIRD ANGLE PROJECTION	
NONE		02947-42	
ECN		SIZE	
02947-42		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	2/16/15	JSP	WJM	RAR	A. UPDATED DRAWING TITLE BLOCK.	02947-42

D10100DA/14