


Mini-Com™ デュプレックスLCアダプタモジュール ジルコニアスリーブ (OS1/OS2用)

Part Numbers: CMDSLCZ■■■

©Panduit Corporation Japan Branch



製品仕様

材質	アダプタ・ハウジング	合成樹脂
	モジュール・ベース	ABS・合成樹脂
	スリーブ	ジルコニアセラミック
	ダスト・キャップ	合成樹脂

電気的性能

伝送性能	挿入損失量	0.75 [dB] 以下
	反射減衰量	40 [dB] 以上
	挿抜耐久性	500 回以上

環境性能

使用環境	使用温度範囲	0 ~ +60 [°C]
	設置場所	事務所・住宅等の屋内のみ (水気・直射日光・機械的衝撃・過重等は厳禁)

寸法 詳細は別紙寸法図を参照(寸法はインチとなり、[]内はメートル表示です)

公称寸法	W 15.8 × D 34.8 × H 18.0 [mm] (公差 ±0.8 [mm])
------	--

質量

公称重量	4.44 [g]
------	----------

カラー

カラー	アダプタ・ハウジング	BU (青)
	モジュール・ハウジング	■■■ : 5色 IW (オフホワイト), IG (ライトグレー), EI (アイボリー), BL (黒), WH (白)

含有化学物質調査

調査項目	RoHS 対応済み	現用品
------	-----------	-----

版	制定	作成	承認
03	2013年10月17日	伊達	高山

Mini-Com™ デュプレックスLCアダプタモジュール ジルコニアスリーブ (OS1/OS2用)

Part Numbers: CMDSLCZ■■■

©Panduit Corporation Japan Branch

改版履歴

版数	改版日	変更内容	担当
01	2007.07.27	初版制定	山之内
02	2011.10.06	製品名称を現仕様に合わせて修正	谷島
03	2013.10.17	製品仕様更新／寸法更新／質量更新	伊達



版	制定	作成	承認
03	2013年10月17日	伊達	高山

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
CMDSLC**	.10 lbs/10 Pcs [44.7 g/10 Pcs]	PHOS BRONZE
CMDSAQLC**		
CMDSLCZ**	.10 lbs/10 Pcs [44.4 g/10 Pcs]	ZIRCONIA
CMDSAQLCZ**		

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- MATERIALS:
 - MODULE BASE: ABS
 - ADAPTER HOUSING: PLASTIC
 - SPLIT SLEEVE: SEE TABLE
 - DUST CAP: PLASTIC
- COMPATIBLE WITH TIA/EIA-604-10 (FOCIS-10) AND TIA/EIA-568B.3
- DIMENSIONS IN BRACKETS ARE METRIC [mm]




REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	03-11-05	MC		RELEASED TO PRODUCTION	00948-17				

MINI-COM LC SENIOR/SENIOR
 DUPLEX FIBER OPTIC ADAPTER MODULE
 CUSTOMER DRAWING



PANDUIT™
 CORP.
 TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,
 UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ±.03 | (.XXX) ±.010 | (.3) ±.005
 (.XX) ±.03 | (.8) ANGLES

DRAWING FILENAME
 M00948AJ_DC_00B.prt
 SCALE
 NONE

DRAWN BY
 MC
 DATE
 06-26-03
 CHK'D
 KWR

REVIEW DRAWING NUMBERS
 SEE NOTES

PART NO.
 SEE TABLE
 DRAWING NO.
 00948-17
 SIZE
 A