


2ポストオープンラック対応棚板 3U

Part Numbers: SRM19CMV3

©Panduit Corporation Japan Branch



製品仕様

材質	アルミニウム
----	--------

環境性能

使用環境	使用温度範囲	-10 ~ +60 [°C]
	使用湿度範囲	25 ~ 85 [%] (結露なきこと)
	設置場所	事務所・住宅等の屋内のみ (水気・直射日光・機械的衝撃・過重等は厳禁)

寸法 詳細は別紙寸法図を参照(寸法はインチとなり、[]内はメートル表示です)

公称寸法	W 488.7 × D 316.2 × H 132.8 [mm] (公差 ±0.8 [mm])
------	---

重量

公称重量	2636 [g]
最大搭載重量	90.7 [kg]

取付

19 インチラック	3 ラックユニット 表面&裏面 各1個
-----------	---------------------

カラー

カラー	BL (黒)
-----	--------

添付品

パネル取付ネジ	8 本キット	(#12-24 × 0.5)
---------	--------	------------------

含有化学物質調査

調査項目	RoHS 対応済み	現用品
------	-----------	-----

版	制定	作成	承認
03	2008年8月8日	山之内	新田

2ポストオープンラック対応棚板 3U

Part Numbers: SRM19CMV3





©Panduit Corporation Japan Branch

改版履歴

版数	改版日	変更内容	担当
01	2007.03.30	初版制定	山之内
02	2007.07.20	含有化学物質調査を追加	山之内
03	2008.08.08	含有化学物質調査結果の表示を変更	山之内

版	制定	作成	承認
03	2008年8月8日	山之内	新田

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
SRM19CMV3	5.81 LBS/EACH 2636 g/EACH

NOTES:

1. IDENTIFICATION: 3RU CENTER RACK MOUNT 19" SHELF WITH VENTS

PART NO. SRM19CMV3 COLOR BLACK

2. COMPONENTS:

(2) SHELVES
(2) PACKS OF #12-24 MOUNTING SCREWS

3. DIMENSIONS IN PARENTHESIS ARE METRIC.
4. LOAD RATING OF 200LBS WHEN BOTH PIECES ARE MOUNTED ON A 3" CHANNEL RACK. (AS SHOWN BELOW)

MODEL FILENAME M10009B0_SRM19HD2P3W_01.PRT

CAD FILENAME/LAYERS M10009B0_DC_01A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

19" CENTER RACK MOUNT SHELF (SRM19CMV3) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± .04 (.XXX) ± .01
(.XX) ± .03 ANGLES ± 1°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JDWE

MAT'L:

SCALE NONE

R	11-8-01	JDWE		RELEASED TO PRODUCTION	10009-08					
---	---------	------	--	------------------------	----------	--	--	--	--	--

DATE 11-8-01

ALUMINUM

DRAWING NO.

10009-08

DWG SIZE A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
-----	------	----	-----	-------------	-----	---	------	-----	-----