

製品仕様

構成	2 ラックユニットのトレイにスラック・スプールを 6 個配置した管理パネル	
材質	トレイ	C.R.S
	スラック・スプール	ABS・合成樹脂
	曲げ保護ポスト	PZBR4

環境性能

使用環境	使用温度範囲	-10 ~ +60 [°C]
	使用湿度範囲	25 ~ 85 [%] (結露なきこと)
	設置場所	事務所・住宅等の屋内のみ (水気・直射日光・機械的衝撃・過重等は厳禁)

寸法 詳細は別紙寸法図を参照(寸法はインチとなり、[]内はメートル表示です)

公称寸法	W 489.92 × D 336.58 × H 82.88 [mm] (公差 ± [mm])
------	--

質量

公称重量	2.27 [kg]
------	-----------

取付

19 インチラック	2 ラック ユニット
-----------	------------

カラー

カラー	トレイ	黒色
	スラック・スプール	黒色

添付品

曲げ保護ポスト	4 本	PZBR4 2 セット
スラック・スプール	6 個	
ラック取付ネジ	4 本	#12-24 × 12.7

版	制定	作成	承認
01	2007 年 8 月 6 日	山之内	新田

含有化学物質調査


調査項目	RoHS 対応済み	現用品
------	-----------	-----

改版履歴

版数	改版日	変更内容	担当
01	2007.08.06	初版制定	山之内

版	制定	作成	承認
01	2007年8月6日	山之内	新田



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
PZCHSM2	5.0 LBS/EACH 2.27 Kg/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) VENTED TRAY
(6) SLACK SPOOLS
(2) PZBR4
(4) #12-24 X .5" SCREWS
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- DIMENSIONS PROVIDED FOR REFERENCE ONLY.



MODEL FILENAME V10290AQ_9RU_HORMGR_ASSY_08.PRT

CAD FILENAME/LAYERS V10290AQ_DC_00C.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

HORIZONTAL SLACK MANAGER (PZCHSM2)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 INCHES X.X, X.XX, X.XXX | [METRIC - MILLIMETER] X, X.X, X.XX | ANGLE +/-

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
02	03-28-07	MAV		B. ADDED VIEWS / DIMENSIONS	10290-64				
01	03-5-07	DSI	BAS	A. CHANGED SCREW DIMENSION	10290-64		BAS		
00	12-6-06	MAV	BAS	RELEASED TO PRODUCTION	10290-64		BAS		

DRAWN BY MAV
DATE 12-6-06
CHK'D BAS

MAT'L:

N/A

SCALE NONE

DRAWING NO.

10290-64

DWG
A
SIZE