


### シングルパンチダウン工具

Part Numbers: PDT110

©Panduit Corporation Japan Branch



### 製品仕様

構成	ハンドル	110仕様
	刃	パンドウイト仕様

### 環境性能

使用環境	使用温度範囲	-10 ~ +60 [°C]
	使用湿度範囲	25 ~ 85 [%] (結露なきこと)

**寸法** 詳細は別紙寸法図を参照 (寸法はインチとなり、[ ]内はメートル表示です)

公称寸法	W 36.5 × L 142.9 × H 27.0 [mm] (公差 ±1.6 [mm])
------	---

### 質量

公称重量	127.0 [g]
------	-----------

### 含有化学物質調査


調査項目	RoHS 対応済み	対象外
------	-----------	-----

### 改版履歴

版数	改版日	変更内容	担当
01	2005.09.30	初版制定	山之内
02	2008.10.14	含有化学物質調査を追加	山之内

版	制定	作成	承認
02	2008年10月14日	山之内	新田

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	DESCRIPTION	WEIGHT
PDT110	TOOL AND BLADE FOR 110 STYLE IDC S.	.28 LB/EACH (127 g/EACH)
PDTH110	REPLACEMENT BLADE FOR 110 STYLE IDC S.	.04 LB/EACH (17 g/EACH)

NOTES:

- \*1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. BLADES CAN BE ORDERED SEPARATELY.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

CAD FILENAME/LAYERS		M00665AX_DC_00A.PRT	
<h1>PANDUIT</h1> <p>CORP. TINLEY PARK, ILLINOIS</p> <p>110 STYLE PUNCH DOWN IMPACT TOOL (PDT)</p> <p>CUSTOMER DRAWING</p>			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± (.XX) ± .062 (1.6) ANGLES ±		(.XXX) ± INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JsP	MAT'L:		SCALE NONE
DATE 11-22-99			DRAWING NO. 00665-23
CHK'D			DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	11-22-99	JsP		RELEASED TO PRODUCTION	00665-23				